

# RTD0100-06-030-H Cut Sheet



ProSense temperature sensor, Pt100 RTD, M12 probe, 360mm insertion length, 6mm probe diameter, stainless steel sheath, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RTD0100-06-030-H>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Temperature sensor
<b>Sensor Element</b>	Pt100 RTD
<b>Sensor Type</b>	M12 probe
<b>Accuracy</b>	Class A accuracy
<b>Insertion Length</b>	360mm
<b>Probe Diameter</b>	6mm
<b>Sheath Material</b>	Stainless steel
<b>Electrical Connection</b>	4-pin M12 quick-disconnect
<b>Temperature Sensing Range</b>	-40 to 302 deg F
<b>Additional Information</b>	Purchase cable and mounting fitting (p/n CF06-25N) separately

## Agency Approvals

<b>UL Listed File #</b>	E324411
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>