

RTD1-B01L06-01 Cut Sheet



ProSense temperature sensor, Pt100 RTD, bolt-on ring, brass sheath, #6 - #10 (4-5mm) screw or bolt size process connection, 6ft 24 AWG wire leads.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RTD1-B01L06-01>

Technical Specifications

| | |
|---------------------------|-------------------------------------|
| Brand | ProSense |
| Item | Temperature sensor |
| Sensor Element | Pt100 RTD |
| Sensor Type | Bolt-on ring |
| Accuracy | Class A accuracy |
| Sheath Material | Brass |
| Process Connection | #6 - #10 (4-5mm) screw or bolt size |
| Electrical Connection | 6ft 24 AWG wire leads |
| Conductor | Carbon steel |
| Insulation Material | Carbon steel |
| Temperature Sensing Range | -58 to 572 deg F |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/RTD1-B01L06-01.pdf>
See store item page for other formats.