


RTD1-B02L06-01 Cut Sheet



ProSense temperature sensor, Pt100 RTD, bolt-on ring, brass sheath, #12, 1/4 to 5/16in (5mm to 8mm) screw or bolt size process connection, 6ft 24 AWG wire leads.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RTD1-B02L06-01>

Technical Specifications

Brand	ProSense
Item	Temperature sensor
Sensor Element	Pt100 RTD
Sensor Type	Bolt-on ring
Accuracy	Class A accuracy
Sheath Material	Brass
Process Connection	#12, 1/4 to 5/16in (5mm to 8mm) screw or bolt size
Electrical Connection	6ft 24 AWG wire leads
Conductor Insulation Material	Kapton and stainless steel overbraid
Temperature Sensing Range	-58 to 572 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document