

RTD1-S15-030-H Cut Sheet



ProSense temperature sensor, Pt100 RTD, sanitary connection probe, 30mm insertion length, 6mm probe diameter, stainless steel sheath, 1-1/2in sanitary tri-clamp process connection, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RTD1-S15-030-H>

Technical Specifications

Brand	ProSense
Item	Temperature sensor
Sensor Element	Pt100 RTD
Sensor Type	Sanitary connection probe
Media Type	Liquid, water, oil, chemicals, gases and air
Accuracy	Class A accuracy
Insertion Length	30mm

Probe Diameter	6mm
Sheath Material	Stainless steel
Process Connection	1-1/2in sanitary tri-clamp
Electrical Connection	4-pin M12 quick-disconnect
Temperature Sensing Range	-58 to 302 deg F
Application	Food and beverage
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	None
UL Recognized File #	E311366
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	3-A Document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/RTD1-S15-030-H.pdf>
See store item page for other formats.