

RTD180-9000 Cut Sheet



AutomationDirect RTD180 series thermal overload relay, 60.0-90.0A adjustable, bi-metallic, pass through connection(s), panel mount. For use with GH15KT, GH15LT or GH15MT 79mm contactors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RTD180-9000>

Technical Specifications

Brand	AutomationDirect
Item	Relay
Series	RTD180
Relay Type	Thermal overload
Full Load Amperage Range	60.0-90.0A adjustable
Operation Type	Bi-metallic
Auxiliary Contacts	(1) N.O. / (1) N.C.
Trip Class	Trip Class 10
Phase Loss Sensitive	Yes
Connection	Pass through
Mounting	Panel
For Use With	GH15KT, GH15LT or GH15MT 79mm contactors

Agency Approvals

UL Listed File #	E191059
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/RTD180-9000.pdf>
See store item page for other formats.