

RTD32-1100 Cut Sheet



AutomationDirect RTD32 series thermal overload relay, 8.0-11.0A adjustable, bi-metallic, direct mount power connection(s), DIN rail mount. For use with GH15BN or GH15CN 45mm contactors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RTD32-1100>

Technical Specifications

| | |
|--------------------------|----------------------------------|
| Brand | AutomationDirect |
| Item | Relay |
| Series | RTD32 |
| Relay Type | Thermal overload |
| Full Load Amperage Range | 8.0-11.0A adjustable |
| Operation Type | Bi-metallic |
| Auxiliary Contacts | (1) N.O. / (1) N.C. |
| Trip Class | Trip Class 10A |
| Phase Loss Sensitive | Yes |
| Connection | Direct mount power |
| Mounting | DIN rail |
| For Use With | GH15BN or GH15CN 45mm contactors |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E191072 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |