

RTD320-32000 Cut Sheet



AutomationDirect RTD320 series thermal overload relay, 216.0-320.0A adjustable, bi-metallic, pass through connection(s), panel mount. For use with GH15ST or GH15TT 145mm contactors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RTD320-32000>

Technical Specifications

Brand	AutomationDirect
Item	Relay
Series	RTD320
Relay Type	Thermal overload
Full Load Amperage Range	216.0-320.0A adjustable
Operation Type	Bi-metallic
Auxiliary Contacts	(1) N.O. / (1) N.C.
Trip Class	Trip Class 10
Phase Loss Sensitive	Yes
Connection	Pass through
Mounting	Panel
For Use With	GH15ST or GH15TT 145mm contactors

Agency Approvals

UL Listed File #	E191059
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document