

RTD65-2800 Cut Sheet



AutomationDirect RTD65 series thermal overload relay, 20.0-28.0A adjustable, bi-metallic, direct mount power connection(s). For use with GH15GT, GH15HT, or GH15JT 60mm contactors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RTD65-2800>

Technical Specifications

Brand	AutomationDirect
Item	Relay
Series	RTD65
Relay Type	Thermal overload
Full Load Amperage Range	20.0-28.0A adjustable
Operation Type	Bi-metallic
Auxiliary Contacts	(1) N.O. / (1) N.C.
Trip Class	Trip Class 10A
Phase Loss Sensitive	Yes
Connection	Direct mount power
For Use With	GH15GT, GH15HT, or GH15JT 60mm contactors

Agency Approvals

UL Listed File #	E191072
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document