

# RTDW-22-1U-P-1 Cut Sheet

TE Wire & Cable RTD extension wire, unshielded, 3 conductors, 22 AWG, tinned copper, PVC conductor insulation material, (1) white and (2) red, PVC jacket, white, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RTDW-22-1U-P-1>

## Technical Specifications

<b>Brand</b>	TE Wire & Cable
<b>Item</b>	Wire
<b>Sensor Type</b>	RTD
<b>Wire/Cable Type</b>	Extension
<b>Application</b>	Temperature
<b>Flexibility</b>	Semi-flexible
<b>Voltage Rating</b>	300V
<b>Conductors</b>	3 conductors
<b>Conductor Size</b>	22 AWG
<b>Conductor Stranding</b>	7/30-stranded
<b>Conductor Material</b>	Tinned copper
<b>Conductor Insulation Material</b>	PVC

<b>Conductor Insulation Color</b>	(1) white and (2) red
<b>Shielding</b>	Unshielded
<b>Jacket Material</b>	PVC
<b>Jacket Color</b>	White
<b>Nominal Overall Cable Diameter</b>	0.16in
<b>Bulk Length</b>	Cut to length
<b>Package Type</b>	<ul style="list-style-type: none"><li>• 50 to 99ft = Coil</li><li>• 100 to 1525ft = 14 x 7in Reel</li><li>• 1526 to 2175ft = 14 x 10in Reel</li><li>• 2176 to 3335ft = 16 x 10in Reel</li><li>• 3336 to 4665ft = 18 x 10in Reel</li><li>• 4666 to 5000ft = 18 x 13in Reel</li></ul>

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>