

RTDW-22-1U-P-1 Cut Sheet

TE Wire & Cable RTD extension wire, unshielded, 3 conductors, 22 AWG, tinned copper, PVC conductor insulation material, (1) white and (2) red, PVC jacket, white, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RTDW-22-1U-P-1>

Technical Specifications

| | |
|--------------------------------------|-----------------------|
| Brand | TE Wire & Cable |
| Item | Wire |
| Sensor Type | RTD |
| Wire/Cable Type | Extension |
| Application | Temperature |
| Flexibility | Semi-flexible |
| Voltage Rating | 300V |
| Conductors | 3 conductors |
| Conductor Size | 22 AWG |
| Conductor Stranding | 7/30-stranded |
| Conductor Material | Tinned copper |
| Conductor Insulation Material | PVC |
| Conductor Insulation Color | (1) white and (2) red |

| | |
|---------------------------------------|---|
| Shielding | Unshielded |
| Jacket Material | PVC |
| Jacket Color | White |
| Nominal Overall Cable Diameter | 0.16in |
| Bulk Length | Cut to length |
| Package Type | 1 to 250ft = Coil, 251 to 1446ft = 14 x 7in Reel, 1447 to 2066ft = 14 x 10in Reel, 2067 to 3196ft = 16 x 10in Reel, 3197 to 4501ft = 18 x 10in Reel, 4502 to 5852ft = 18 x 13in Reel, 5853 to 12570ft = 24 x 17in Wooden Reel, 12571 to 20667ft = 30 x 17in Wooden Reel, 20668 to MAX = Large Wooden Reel |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |