

RTDW-24-1S-F-1 Cut Sheet

TE Wire & Cable RTD extension wire, shielded, 3 conductors, 24 AWG, tinned copper, FEP Teflon conductor insulation material, (1) white and (2) red, FEP Teflon jacket, white, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RTDW-24-1S-F-1>

Technical Specifications

Brand	TE Wire & Cable
Item	Wire
Sensor Type	RTD
Wire/Cable Type	Extension
Application	Temperature
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	3 conductors
Conductor Size	24 AWG
Conductor Stranding	7/32-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	FEP Teflon
Conductor Insulation Color	(1) white and (2) red

Shielding	Shielded
Jacket Material	FEP Teflon
Jacket Color	White
Nominal Overall Cable Diameter	0.133in
Bulk Length	Cut to length
Package Type	1 to 250ft = Coil, 251 to 2093ft = 14 x 7in Reel, 2094 to 2990ft = 14 x 10in Reel, 2991 to 4626ft = 16 x 10in Reel, 4627 to 6515ft = 18 x 10in Reel, 6516 to 8469ft = 18 x 13in Reel, 8470 to 18192ft = 24 x 17in Wooden Reel, 18193 to 29910ft = 30 x 17in Wooden Reel, 29911 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document
Other	RoHS Statement