

# RTDW-24-1S-F-1 Cut Sheet

TE Wire & Cable RTD extension wire, shielded, 3 conductors, 24 AWG, tinned copper, FEP Teflon conductor insulation material, (1) white and (2) red, FEP Teflon jacket, white, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RTDW-24-1S-F-1>

## Technical Specifications

<b>Brand</b>	TE Wire & Cable
<b>Item</b>	Wire
<b>Sensor Type</b>	RTD
<b>Wire/Cable Type</b>	Extension
<b>Application</b>	Temperature
<b>Flexibility</b>	Semi-flexible
<b>Voltage Rating</b>	300V
<b>Conductors</b>	3 conductors
<b>Conductor Size</b>	24 AWG
<b>Conductor Stranding</b>	7/32-stranded
<b>Conductor Material</b>	Tinned copper
<b>Conductor Insulation Material</b>	FEP Teflon

<b>Conductor Insulation Color</b>	(1) white and (2) red
<b>Shielding</b>	Shielded
<b>Jacket Material</b>	FEP Teflon
<b>Jacket Color</b>	White
<b>Nominal Overall Cable Diameter</b>	0.133in
<b>Bulk Length</b>	Cut to length
<b>Package Type</b>	<ul style="list-style-type: none"><li>• 50 to 99ft = Coil</li><li>• 100 to 2205ft = 14 x 7in Reel</li><li>• 2206 to 3150ft = 14 x 10in Reel</li><li>• 3151 to 4830ft = 16 x 10in Reel</li><li>• 4831 to 5000ft = 18 x 10in Reel</li></ul>

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>