

# RTH-D20QA-ND0 Cut Sheet



Contrinex basic RFID tag, round, 20mm diameter, non-flush mount, HF communication, 13.56 MHz, FRAM memory, 2048 bytes, IP68 IP69K.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RTH-D20QA-ND0>

## Technical Specifications

<b>Brand</b>	Contrinex
<b>Item</b>	RFID tag
<b>Tag Type</b>	Basic
<b>Shape</b>	Round
<b>Size</b>	20mm diameter
<b>Mounting</b>	Non-flush
<b>Communication Type</b>	HF
<b>RFID Frequency</b>	13.56 MHz
<b>Memory Type</b>	FRAM
<b>Total Memory</b>	2048 bytes
<b>User Memory</b>	2000 bytes
<b>Material</b>	Polyphthalamide
<b>IP Rating</b>	IP68 IP69K
<b>Operating Temperature</b>	-25 degrees to 80 degrees C

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/RTH-D20QA-ND0.pdf>  
See store item page for other formats.