

# RTH-D26RV-ECO Cut Sheet



Contrinex high temperature RFID tag, round, 26mm diameter, flush mount, HF communication, 13.56 MHz, EEPROM memory, 128 bytes, IP68 IP69K.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RTH-D26RV-ECO>

## Technical Specifications

|                              |                       |
|------------------------------|-----------------------|
| <b>Brand</b>                 | Contrinex             |
| <b>Item</b>                  | RFID tag              |
| <b>Tag Type</b>              | High temperature      |
| <b>Shape</b>                 | Round                 |
| <b>Size</b>                  | 26mm diameter         |
| <b>Mounting</b>              | Flush                 |
| <b>Communication Type</b>    | HF                    |
| <b>RFID Frequency</b>        | 13.56 MHz             |
| <b>Memory Type</b>           | EEPROM                |
| <b>Total Memory</b>          | 128 bytes             |
| <b>User Memory</b>           | 112 bytes             |
| <b>Material</b>              | Polyphenylene sulfide |
| <b>IP Rating</b>             | IP68 IP69K            |
| <b>Operating Temperature</b> | -25 degrees to 180 °C |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/RTH-D26RV-ECO.pdf>  
See store item page for other formats.