

RTH-D50QA-NF0 Cut Sheet



Contrinex basic RFID tag, round, 50mm diameter, non-flush mount, HF communication, 13.56 MHz, EEPROM memory, 320 bytes, IP68 IP69K.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RTH-D50QA-NF0>

Technical Specifications

Brand	Contrinex
Item	RFID tag
Tag Type	Basic
Shape	Round
Size	50mm diameter
Mounting	Non-flush
Communication Type	HF
RFID Frequency	13.56 MHz
Memory Type	EEPROM
Total Memory	320 bytes
User Memory	316 bytes
Material	Polyphthalamide
IP Rating	IP68 IP69K
Operating Temperature	-25 degrees to 80 degrees C

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/RTH-D50QA-NF0.pdf>
See store item page for other formats.