


RV8-4916D Cut Sheet



Trumeter electromechanical counter, 4mm 6-digit analog, 24 VDC input, rectangular 2-hole/4-hole base mount, (2) 11in 22 AWG pigtails.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RV8-4916D>

Technical Specifications

Brand	Trumeter
Item	Counter
Counter Type	Electromechanical
Count Direction	Up
Count Speed	10Hz
Display Type	Analog
Display Size	4mm 6-digit
Input	24 VDC
Operating Voltage	24 VDC
Mounting	Panel or base
Mounting Type	Rectangular 2-hole/4-hole base mount
Mounting Hole Size	1.46 x 1.01in
Connector Type	(2) 11in 22 AWG pigtails
Includes	Diode protection

Agency Approvals

UL Listed File #	None
UL Recognized File #	E36690
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document