

RWRE-00-0A Cut Sheet



ProSense photoelectric sensor, rectangular, ABS plastic housing, through-beam emitter, visible red, 3m sensing distance, 10-30 VDC operating voltage, 2-wire, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RWRE-00-0A>

Technical Specifications

Brand	ProSense
Item	Photoelectric sensor
Shape	Rectangular
Housing Size	14.4 x 8.1 x 28.1mm
IP Rating	IP65 IP67
Housing Material	ABS plastic
Sensing Method	Through-beam emitter
Operating Voltage	10-30 VDC

Number of Wires	2
Sensing Distance	3m
Light Emission (NP)	Visible red
IO-Link Compatible	No
Cable Length	6.5ft/2m
Jacket Material	Carbon steel
Connection	Pigtail
Conductor Size	28 AWG

Agency Approvals

UL Listed File #	E328811
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/RWRE-00-0A.pdf>
See store item page for other formats.