

# RWRR-DP-0A Cut Sheet



ProSense photoelectric sensor, rectangular, ABS plastic housing, through-beam receiver, visible red light emission, 3m sensing distance, 10-30 VDC operating voltage, dark-on, PNP, 3-wire, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RWRR-DP-0A>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Photoelectric sensor
<b>Shape</b>	Rectangular
<b>Housing Size</b>	14.4 x 8.1 x 28.1mm
<b>IP Rating</b>	IP65 IP67
<b>Housing Material</b>	ABS plastic
<b>Sensing Method</b>	Through-beam receiver
<b>Operating Voltage</b>	10-30 VDC
<b>Number of Wires</b>	3
<b>Switching Output</b>	PNP
<b>Sensing Distance</b>	3m
<b>Operation Mode</b>	Dark-on
<b>Switching Frequency</b>	1000 Hz
<b>Light emission</b>	Visible red
<b>IO-Link Compatible</b>	No
<b>Cable Length</b>	6.5ft/2m
<b>Jacket Material</b>	PVC
<b>Connection</b>	Pigtail
<b>Conductor Size</b>	28 AWG

## Agency Approvals

<b>UL Listed File #</b>	E328811
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>