RWRS-LP-5A Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

ProSense photoelectric sensor, rectangular, background suppression, visible red, 1–50mm sensing distance, light-on, PNP, 14.4 x 8.1 x 28.1mm body, ABS plastic, 6.5ft/2m cable length, pigtail.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/RWRS-LP-5A

Technical Specifications

Brand	ProSense
Item	Photoelectric sensor
Shape	Rectangular
IP Rating	IP65 IP67
Application	Standard duty
Housing Size	14.4 x 8.1 x 28.1mm body
Housing Material	ABS plastic
Sensing Method	Background suppression
Operating Voltage	10–30 VDC
Switching Output	PNP

Sensing Distance	1–50mm
Operation Mode	Light-on
Switching Frequency	1000 Hz
Light Emission	Visible red
IO-Link Compatible	No
Cable Length	6.5ft/2m
Jacket Material	PVC
Connection	Pigtail
Number of Wires	3
Conductor Size	28 AWG

Agency Approvals

UL Listed File #	E328811
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/RWRS-LP-5A.pdf
See store item page for other formats.