

S-4/0-250-1 Cut Sheet



Penn-Union S series split bolt, copper alloy, 15/16in nut hex, 1-1/8in body hex, 10 AWG-250 MCM, copper.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/S-4/0-250-1>

Technical Specifications

Brand	Penn-Union
Series	S
Item	Split bolt
Material	Copper alloy
Nut Hex Size	15/16in
Body Hex Size	1-1/8in
Number Of Conductors	2
Conductor Size	10 AWG-250 MCM
Conductor Material	Copper

Agency Approvals

UL Listed File #	E12822
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	023769
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/S-4_0-250-1.pdf
See store item page for other formats.