

S34CX0 Cut Sheet



RuB S34 manual mini ball valve, 2-port (2-way), 2-position, rotary lever, 3/8in female NPT inlet(s), 3/8in female NPT outlet(s), Cv=4.2.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/S34CX0>

Technical Specifications

| | |
|----------------------------|--|
| Brand | RuB |
| Item | Valve |
| Working Fluid | Pneumatic, coolant, emulsion, gases, inert gas, oil or water |
| Valve Type | Manual mini ball |
| Series | S34 |
| Port Quantity | 2-port (2-way) |
| Number Of Positions | 2 |
| Operator Type | Rotary lever |
| Body Material | Chrome-plated brass |

| | |
|-----------------------------------|------------------------------|
| Handle Material | Glass fiber reinforced nylon |
| Seal Material | FPM |
| Inlet Port | 3/8in female NPT |
| Outlet Port | 3/8in female NPT |
| Flow Coefficient | 4.2 |
| Maximum Operating Pressure | 200 psi |
| Minimum Operating Pressure | 0 psi |
| Working Fluid Temperature | -4 to +200 °F |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/S34CX0.pdf>
See store item page for other formats.