

# S35CZ0 Cut Sheet



RuB S35 manual mini ball valve, 2-port (2-way), 2-position, rotary lever, 3/8in male NPT inlet(s), 3/8in female NPT outlet(s), Cv=4.2.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/S35CZ0>

## Technical Specifications

<b>Brand</b>	RuB
<b>Item</b>	Valve
<b>Working Fluid</b>	Pneumatic, coolant, emulsion, gases, inert gas, oil or water
<b>Valve Type</b>	Manual mini ball
<b>Series</b>	S35
<b>Port Quantity</b>	2-port (2-way)
<b>Number Of Positions</b>	2
<b>Operator Type</b>	Rotary lever
<b>Body Material</b>	Chrome-plated brass

<b>Handle Material</b>	Glass fiber reinforced nylon
<b>Seal Material</b>	FPM
<b>Inlet Port</b>	3/8in male NPT
<b>Outlet Port</b>	3/8in female NPT
<b>Flow Coefficient</b>	4.2
<b>Maximum Operating Pressure</b>	450 psi
<b>Minimum Operating Pressure</b>	0 psi
<b>Working Fluid Temperature</b>	-4 to +200 °F

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/S35CZ0.pdf>  
See store item page for other formats.