

S39AX0M Cut Sheet



RuB S39 manual micro ball valve, 2-port (2-way), 2-position, wedge handle, 1/8in female NPT inlet(s), 1/8in female NPT outlet(s), Cv=1.4.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/S39AX0M>

Technical Specifications

Brand	RuB
Item	Valve
Working Fluid	Pneumatic, coolant, emulsion, gases, inert gas, oil or water
Valve Type	Manual micro ball
Series	S39
Port Quantity	2-port (2-way)
Number Of Positions	2
Operator Type	Wedge handle
Body Material	Nickel-plated brass

Handle Material	Glass fiber reinforced nylon
Seal Material	FPM
Inlet Port	1/8in female NPT
Outlet Port	1/8in female NPT
Flow Coefficient	1.4
Maximum Operating Pressure	900 psi
Minimum Operating Pressure	0 psi
Working Fluid Temperature	-4 to +200 °F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/S39AX0M.pdf>
See store item page for other formats.