

S61200FCHG Cut Sheet



Atkore Calbrite hygienic connector, liquid-tight, 316 stainless steel, straight, 1-1/4in trade size, compression conduit connection, insulated, polished finish. For use with LFMC electrical conduit. FDA blue seal included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/S61200FCHG>

Technical Specifications

Brand	Atkore
Series	Calbrite
Item	Connector
Application	Hygienic
Liquid-tight	Yes
Fitting Type	Straight
Material	316 stainless steel
Trade Size	1-1/4in
Conduit Connection Method	Compression
Box Connection Type	1-1/4in male NPSM
Insulated	Yes

Finish	Polished
Knockout Size	1-1/4in
Liquid-tight Flexible Metal Conduit (LFMC) Trade Size	1-1/4in
IP Rating	IP66, IP67, IP68 and IP69
UL Type	4X
Operating Temperature	-58 to +275 °F
For Use With	LFMC electrical conduit
Includes	FDA blue seal
Applicable Standards	UL 514B Listed, CSA C22.2 No 18.3 and NSF/ANSI 169

Agency Approvals

UL Listed File #	E247502
UL Recognized File #	none
UL Hazardous File #	none
CSA File #	none
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement