

S92B41 Cut Sheet



RuB S92 manual ball valve, 2-port (2-way), 2-position, rotary lever, 1/4in female NPT inlet(s), 1/4in female NPT outlet(s), Cv=4.5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/S92B41>

Technical Specifications

| | |
|----------------------------|---|
| Brand | RuB |
| Item | Valve |
| Working Fluid | Pneumatic, coolant, emulsion, gases, inert gas, oil, steam or water |
| Valve Type | Manual ball |
| Series | S92 |
| Port Quantity | 2-port (2-way) |
| Number Of Positions | 2 |
| Operator Type | Rotary lever |
| Body Material | Brass |

| | |
|-----------------------------------|-------------------|
| Handle Material | PVC dipped steel |
| Seal Material | PTFE |
| Inlet Port | 1/4in female NPT |
| Outlet Port | 1/4in female NPT |
| Flow Coefficient | 4.5 |
| Maximum Operating Pressure | Varies with fluid |
| Minimum Operating Pressure | 0 psi |
| Working Fluid Temperature | -40 to +366 °F |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | MH15505 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | 112439 |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/S92B41.pdf>
See store item page for other formats.