

S92F41 Cut Sheet



RuB S92 manual ball valve, 2-port (2-way), 2-position, rotary lever, 1in female NPT inlet(s), 1in female NPT outlet(s), Cv=80.9.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/S92F41>

Technical Specifications

Brand	RuB
Item	Valve
Working Fluid	Pneumatic, coolant, emulsion, gases, inert gas, oil, steam or water
Valve Type	Manual ball
Series	S92
Port Quantity	2-port (2-way)
Number Of Positions	2
Operator Type	Rotary lever
Body Material	Brass

Handle Material	PVC dipped steel
Seal Material	PTFE
Inlet Port	1in female NPT
Outlet Port	1in female NPT
Flow Coefficient	80.9
Maximum Operating Pressure	Varies with fluid
Minimum Operating Pressure	0 psi
Working Fluid Temperature	-40 to +366 °F

Agency Approvals

UL Listed File #	MH15505
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	112439
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/S92F41.pdf>
See store item page for other formats.