

S93C41 Cut Sheet



RuB S93 pneumatic manual ball valve, 3-port (3-way), 2-position, lockable rotary lever, 3/8in female NPT inlet(s), 3/8in female NPT outlet(s), #10-32 female threaded exhaust(s), Cv=9.5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/S93C41>

Technical Specifications

Brand	RuB
Item	Valve
Working Fluid	Air
Valve Type	Manual ball
Series	S93
Port Quantity	3-port (3-way)
Number Of Positions	2
Operator Type	Lockable rotary lever
Body Material	Brass

Handle Material	PVC dipped steel
Seal Material	FPM
Inlet Port	3/8in female NPT
Outlet Port	3/8in female NPT
Exhaust Port	#10-32 female threaded
Flow Coefficient	9.5
Maximum Operating Pressure	200 psi
Minimum Operating Pressure	0 psi
Working Fluid Temperature	15-210 °F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/S93C41.pdf>
See store item page for other formats.