

S95B45 Cut Sheet



RuB S95 manual ball valve, 2-port (2-way), 2-position, lockable rotary lever, 1/4in female NPT inlet(s), 1/4in female NPT outlet(s), Cv=4.5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/S95B45>

Technical Specifications

Brand	RuB
Item	Valve
Working Fluid	Pneumatic, coolant, emulsion, gases, inert gas, oil or water
Valve Type	Manual ball
Series	S95
Port Quantity	2-port (2-way)
Number Of Positions	2
Operator Type	Lockable rotary lever
Body Material	Brass

Handle Material	PVC dipped steel
Seal Material	FPM
Inlet Port	1/4in female NPT
Outlet Port	1/4in female NPT
Flow Coefficient	4.5
Maximum Operating Pressure	Varies with fluid
Minimum Operating Pressure	0 psi
Working Fluid Temperature	-40 to +350 °F

Agency Approvals

UL Listed File #	MH15505
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	112439
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/S95B45.pdf>
See store item page for other formats.