

S95E41MR Cut Sheet



RuB S95 manual ball valve, 2-port (2-way), 2-position, N.C., rotary lever, spring return, 3/4in female NPT inlet(s), 3/4in female NPT outlet(s), Cv=48.5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/S95E41MR>

Technical Specifications

Brand	RuB
Item	Valve
Working Fluid	Pneumatic, coolant, emulsion, gases, inert gas, oil or water
Valve Type	Manual ball
Series	S95
Port Quantity	2-port (2-way)
Number Of Positions	2
Valve Configuration	N.C.
Operator Type	Rotary lever
Action	Spring return

Body Material	Brass
Handle Material	PVC dipped steel
Seal Material	FPM
Inlet Port	3/4in female NPT
Outlet Port	3/4in female NPT
Flow Coefficient	48.5
Maximum Operating Pressure	Varies with fluid
Minimum Operating Pressure	0 psi
Working Fluid Temperature	-40 to +350 °F

Agency Approvals

UL Listed File #	MH15505
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	112439
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/S95E41MR.pdf>
See store item page for other formats.