


SAC-18-4U-2YL-1 Cut Sheet



AutomationDirect flexible sensor/actuator cable, unshielded, 4 conductors, 18 AWG, bare copper, PVC conductor insulation material, black, white, red and green/yellow, PVC jacket, yellow, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SAC-18-4U-2YL-1>

Technical Specifications

Brand	AutomationDirect	Conductor Insulation Color	Black, white, red and green/yellow
Item	Cable	Shielding	Unshielded
Wire/Cable Type	Sensor/actuator	Jacket Material	PVC
UL Wire/Cable Type	AWM	Jacket Color	Yellow
Applicable Standards	UL 2464	Nominal Overall Cable Diameter	0.228 in
Application	Sensor/actuator	Bulk Length	Cut to length
Flexibility	Flexible	Package Type	• 30–99 ft = Coil • 100–750 ft = 14 x 7 in Reel • 751–1070 ft = 14 x 10 in Reel • 1071–1645 ft = 16 x 10 in Reel • 1646–2295 ft = 18 x 10 in Reel • 2296–2985 ft = 18 x 13 in Reel • 2986–5000 ft = 24 x 17 in Wooden Reel
Voltage Rating	300 V		
Conductors	4 conductors		
Conductor Size	18 AWG		
Conductor Stranding	16-stranded		
Conductor Material	Bare copper		
Conductor Insulation Material	PVC		

Agency Approvals

UL Listed File #	None
UL Recognized File #	E505482
UL Hazardous File #	None
CSA File #	LL274638
RoHS Status	No
EU REACH	View EU REACH document