

SADS-35C-15.87-15.87 Cut Sheet



Sung-II Machinery drive coupling, advanced disc, aluminum alloy, clamp, size 35, 5/8 x 5/8in bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SADS-35C-15.87-15.87>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling
Coupling Type	Advanced disc
Material	Aluminum alloy
Rated Torque	6 N·m
Maximum Torque	12 N·m
Maximum Angular Misalignment	1.0 degrees
Maximum Parallel Misalignment	0.02mm
Maximum RPM	8500

Attachment Style	Clamp
Coupling Size	35
Overall Length	27.2mm
Bore Diameter	5/8in
Bore Diameter 2	5/8in
Outside Diameter	35mm
Clamp Screw Fastening Torque	1.7 N·m
Clamp Screw Size	M3-0.5 x 12mm

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SADS-35C-15.87-15.87.pdf>
See store item page for other formats.