

SADS-44C-19.05-22.22 Cut Sheet



Sung-II Machinery drive coupling, advanced disc, aluminum alloy, clamp, size 44, 3/4 x 7/8in bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SADS-44C-19.05-22.22>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling
Coupling Type	Advanced disc
Material	Aluminum alloy
Rated Torque	14 N·m
Maximum Torque	28 N·m
Maximum Angular Misalignment	1.0 degrees
Maximum Parallel Misalignment	0.02mm
Maximum RPM	8000

Attachment Style	Clamp
Coupling Size	44
Overall Length	33.2mm
Bore Diameter	3/4in
Bore Diameter 2	7/8in
Outside Diameter	44mm
Clamp Screw Fastening Torque	3.5 N·m
Clamp Screw Size	M4-0.7 x 14mm

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SADS-44C-19.05-22.22.pdf>
See store item page for other formats.