

SAS542-ADC Cut Sheet



Winters snubber, adjustable stainless steel stem and PTFE seal element, stainless steel body, 1/4in male NPT x 1/4in female NPT.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SAS542-ADC>

Technical Specifications

Brand	Winters
Item	Snubber
Body Material	Stainless steel
Snubbing Element	Adjustable stainless steel stem and PTFE seal
Connection	1/4in male NPT x 1/4in female NPT
Operating Pressure	6,000 psi
Operating Temperature	-40°F to 248°F (-40°C to 120°C)
Application	Recommended to protect pressure gauges and transmitters from pressure surges, spikes, fluctuations, and fluid hammer

Agency Approvals

CE	None
RoHS Status	No
EU REACH	View EU REACH document