

SAS542-ADC Cut Sheet



Winters snubber, adjustable stainless steel stem and PTFE seal element, stainless steel body, 1/4in male NPT x 1/4in female NPT.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SAS542-ADC>

Technical Specifications

Brand	Winters
Item	Snubber
Body Material	Stainless steel
Snubbing Element	Adjustable stainless steel stem and PTFE seal
Connection	1/4in male NPT x 1/4in female NPT
Operating Pressure	6,000 psi
Operating Temperature	-40°F to 248°F (-40°C to 120°C)
Application	Recommended to protect pressure gauges and transmitters from pressure surges, spikes, fluctuations, and fluid hammer

Agency Approvals

CE	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SAS542-ADC.pdf>
See store item page for other formats.