

SBM2K9900W03 Cut Sheet



Comepi safety switch, cable-pull interlock, with reset, 25m maximum pull cable length, (3) N.C. safety output(s), die-cast aluminum body, thermoplastic head, (1) 1/2in NPT cable entry.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SBM2K9900W03>

Technical Specifications

| | |
|---------------------------|---------------------------|
| Brand | Comepi |
| Item | Safety switch |
| Actuator Type | Cable-pull interlock |
| Reset | Yes |
| Action | Slow action |
| Maximum Pull Cable Length | 25m |
| Safety Output Type | (3) N.C. |
| Housing Size | 40 x 170 x 43mm |
| Body Material | Die-cast aluminum |
| Head Material | Thermoplastic |
| IP Rating | IP66 |
| Connection | (1) 1/2in NPT cable entry |
| Additional Information | Purchase cable separately |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E189258 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SBM2K9900W03.pdf>
See store item page for other formats.