

SC11-LS110-0 Cut Sheet



Murrelektronik field wireable solenoid valve connector, 11mm DIN style molded connector, 110 VAC/VDC, 16-12 AWG, accepts cable diameter size 0.24-0.32in, surge protection, LED indication.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SC11-LS110-0>

Technical Specifications

Brand	Murrelektronik
Item	Field wireable solenoid valve connector
Connector Type	11mm DIN style molded connector
Voltage Rating	110 VAC/VDC
Conductor Size	16-12 AWG
Cable Diameter Size	0.24-0.32in
Protection Type(s)	surge
Indicating Type	LED indication

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SC11-LS110-0.pdf>
See store item page for other formats.