

SC121210NK Cut Sheet



Wiegmann enclosure, NEMA 1, 12 x 12 x 10in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SC121210NK>

Technical Specifications

| | |
|-------------------------------------|------------------------|
| Brand | Wiegmann |
| Item | Enclosure |
| Slope Top | No |
| 3-Piece Assembly | No |
| Vented | No |
| NEMA Rating | 1 |
| Nominal Enclosure Dimensions | 12 x 12 x 10in (HxWxD) |
| Enclosure Height | 12.00in |
| Enclosure Width | 12.13in |
| Enclosure Depth | 10.13in |
| Mounting | Wall |
| Integral Mounting Feet | No |

| | |
|---------------------------------|--------------|
| Integral Mounting Flange | No |
| Dual Access | No |
| Knockouts | No |
| Bottom Gland Plate | No |
| Material | Carbon steel |
| Color | ANSI 61 gray |
| Finish | Powder coat |
| Cover Type | Screw cover |
| Shelf | No |
| Padlockable | No |
| Keylocking | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E23553 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SC121210NK.pdf>
See store item page for other formats.