

# SC151504 Cut Sheet



Wiegmann enclosure, NEMA 1, 15 x 15 x 4in (HxWxD), wall mount, with knockouts, carbon steel, ANSI 61 gray, powder coat finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SC151504>

## Technical Specifications

|                                     |                       |
|-------------------------------------|-----------------------|
| <b>Brand</b>                        | Wiegmann              |
| <b>Item</b>                         | Enclosure             |
| <b>Slope Top</b>                    | No                    |
| <b>NEMA Rating</b>                  | 1                     |
| <b>Nominal Enclosure Dimensions</b> | 15 x 15 x 4in (HxWxD) |
| <b>Enclosure Height</b>             | 15.13in               |
| <b>Enclosure Width</b>              | 15.13in               |
| <b>Enclosure Depth</b>              | 4.47in                |
| <b>Mounting</b>                     | Wall                  |
| <b>Integral Mounting Feet</b>       | No                    |
| <b>Integral Mounting Flange</b>     | No                    |
| <b>Dual Access</b>                  | No                    |
| <b>Knockouts</b>                    | Yes                   |
| <b>Material</b>                     | Carbon steel          |
| <b>Color</b>                        | ANSI 61 gray          |
| <b>Finish</b>                       | Powder coat           |
| <b>Cover Type</b>                   | Screw cover           |
| <b>Padlockable</b>                  | No                    |
| <b>Keylocking</b>                   | No                    |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E23553                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |