

SC151806G Cut Sheet



Wiegmann enclosure, NEMA 1, 18 x 15 x 6in (HxWxD), wall mount, with knockouts, galvanized steel, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SC151806G>

Technical Specifications

Brand	Wiegmann
Item	Enclosure
Slope Top	No
NEMA Rating	1
Nominal Enclosure Height	18in
Nominal Enclosure Width	15in
Nominal Enclosure Depth	6in
Mounting	Wall

Integral Mounting Feet	No
Integral Mounting Flange	No
Dual Access	No
Knockouts	Yes
Material	Galvanized steel
Cover Type	Screw cover
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E23553
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SC151806G.pdf>
See store item page for other formats.