

# SC182410GNK Cut Sheet



Wiegmann enclosure, NEMA 1, 24 x 18 x 10in (HxWxD), wall mount, galvanized steel, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SC182410GNK>

## Technical Specifications

|                          |           |
|--------------------------|-----------|
| Brand                    | Wiegmann  |
| Item                     | Enclosure |
| Slope Top                | No        |
| NEMA Rating              | 1         |
| Nominal Enclosure Height | 24in      |
| Nominal Enclosure Width  | 18in      |
| Nominal Enclosure Depth  | 10in      |
| Mounting                 | Wall      |

|                          |                  |
|--------------------------|------------------|
| Integral Mounting Feet   | No               |
| Integral Mounting Flange | No               |
| Dual Access              | No               |
| Knockouts                | No               |
| Material                 | Galvanized steel |
| Cover Type               | Screw cover      |
| Padlockable              | No               |
| Keylocking               | No               |

## Agency Approvals

|                      |                                        |
|----------------------|----------------------------------------|
| UL Listed File #     | E23553                                 |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | None                                   |
| CSA File #           | None                                   |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SC182410GNK.pdf>  
See store item page for other formats.