

SC182412GNK Cut Sheet



Wiegmann enclosure, NEMA 1, 24 x 18 x 12in (HxWxD), wall mount, galvanized steel, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SC182412GNK>

Technical Specifications

| | |
|---------------------------------|-----------|
| Brand | Wiegmann |
| Item | Enclosure |
| Slope Top | No |
| NEMA Rating | 1 |
| Nominal Enclosure Height | 24in |
| Nominal Enclosure Width | 18in |
| Nominal Enclosure Depth | 12in |
| Mounting | Wall |

| | |
|---------------------------------|------------------|
| Integral Mounting Feet | No |
| Integral Mounting Flange | No |
| Dual Access | No |
| Knockouts | No |
| Material | Galvanized steel |
| Cover Type | Screw cover |
| Padlockable | No |
| Keylocking | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E23553 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SC182412GNK.pdf>
See store item page for other formats.