

SC2DD4050 Cut Sheet



Eltwin SC2 series solid state contactor, 50A, (2) N.O. SCR switched power poles, 24-480 VAC (50/60Hz) operating voltage, 5-24 VDC coil voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SC2DD4050>

Technical Specifications

Brand	Eltwin	Operating Voltage	24-480 VAC (50/60Hz)
Item	Contactur	Coil Voltage	5-24 VDC
Series	SC2	Horsepower Rating	10hp
Contactur Type	Solid state	SCCR Rating	5kA SCCR
Actuator Type	Electronic	UL Rating	UL 508 rated
Reversing	No	Protection Type(s)	Varistor surge protection
Amperage Rating	50A	Mounting	35mm DIN rail or panel
Power Poles	(2) N.O. SCR switched	Indicating Type	(1) status LED
Switching Type	Zero cross	Additional Information	Purchase overload protection switch separately

Agency Approvals

UL Listed File #	E207530
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SC2DD4050.pdf>
See store item page for other formats.