

SC311YN02VIAA6 Cut Sheet



CFA solenoid valve, 2-port (2-way), 2-position, N.C., nylon body, Viton seal(s), 1/8in female NPT inlet(s), 1/8in female NPT outlet(s), Cv=0.28, 0 psi minimum operating pressure, 120 VAC operating voltage, 11mm DIN style wiring plug.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SC311YN02VIAA6>

Technical Specifications

Brand	CFA
Item	Valve
Working Fluid	Air, inert gas, water or coolant
Valve Type	Solenoid process
Port Quantity	2-port (2-way)
Number Of Positions	2
Valve Configuration	N.C.
Action	Single solenoid spring return
Body Material	Nylon
Seal Material	Viton
Inlet Port	1/8in female NPT
Outlet Port	1/8in female NPT
Flow Coefficient	0.28
Maximum Operating Pressure	116 psi
Minimum Operating Pressure	0 psi
Working Fluid Temperature	122 deg F maximum
Operating Voltage	120 VAC
Power Rating	6.5 VA
Electrical Connection	11mm DIN style wiring plug

Agency Approvals

UL Listed File #	None
UL Recognized File #	YSY12 - MH17997
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document