

SC6-1100 Cut Sheet



ProSense signal conditioner, isolated, current input, current output, 24 VDC nominal operating voltage, 35mm DIN rail mount, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SC6-1100>

Technical Specifications

Brand	ProSense
Item	Signal conditioner
Isolation	Isolated
Field Configurable	No
Input Current Signal Range	0-20 mA
Output Current Signal Range	0-20 mA
Operating Voltage	24 VDC nominal
Housing Material	Plastic
Mounting	35mm DIN rail
Electrical Connection	Screw terminals

Agency Approvals

UL Listed File #	E498965
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	FM Approval Document