

SC6-1101 Cut Sheet



ProSense signal conditioner, isolated, Input: 1-channel, loop powered current, 0-20 mA, Output: 1-channel, current, 0-20 mA, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SC6-1101>

Technical Specifications

Brand	ProSense
Item	Signal conditioner
Isolation	Isolated
Field Configurable	No
Number Of Input Channels	1
Input	Loop powered current
Input Current Signal Range	0-20 mA

Number Of Output Channels	1
Output	Current
Output Current Signal Range	0-20 mA
Housing Material	Plastic
Mounting	35mm DIN rail
Electrical Connection	Screw terminals
Application	Hazardous location rated

Agency Approvals

UL Listed File #	E498965
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	FM Approval Document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SC6-1101.pdf>
See store item page for other formats.