

# SC6-1110 Cut Sheet



ProSense signal conditioner, isolated, current input, (2) current output, 24 VDC nominal operating voltage, 35mm DIN rail mount, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SC6-1110>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Signal conditioner
<b>Isolation</b>	Isolated
<b>Field Configurable</b>	No
<b>Input Current Signal Range</b>	0-20 mA
<b>Output Current Signal Range</b>	0-20 mA
<b>Output Current Signal Range 2</b>	0-20 mA
<b>Operating Voltage</b>	24 VDC nominal
<b>Housing Material</b>	Plastic
<b>Mounting</b>	35mm DIN rail
<b>Electrical Connection</b>	Screw terminals

## Agency Approvals

<b>UL Listed File #</b>	E498965
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">FM Approval Document</a>