

# SC6-2220 Cut Sheet



ProSense signal conditioner, isolated, current or voltage input, (2) current or voltage output, 24 VDC nominal operating voltage, 35mm DIN rail mount, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SC6-2220>

## Technical Specifications

Brand	ProSense
Item	Signal conditioner
Isolation	Isolated
Field Configurable	Yes
Input Current Signal Range	Input current signal range(s) of 0-20 mA, 4-20 mA
Input Voltage Signal Range	Input voltage signal range(s) of 0-5 VDC, 1-5 VDC, 0-10 VDC, 2-10 VDC
Output Current Signal Range	0-20 mA and 4-20 mA
Output Current Signal Range 2	0-20 mA and 4-20 mA

Output Voltage Signal Range	0-5 VDC, 1-5 VDC, 0-10 VDC and 2-10 VDC
Output Voltage Signal Range 2	2-10 VDC, 0-5 VDC, 1-5 VDC and 0-10 VDC
Operating Voltage	24 VDC nominal
Housing Material	Plastic
Mounting	35mm DIN rail
Electrical Connection	Screw terminals

## Agency Approvals

UL Listed File #	E498965
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">FM Approval Document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SC6-2220.pdf>  
See store item page for other formats.