

SC6-4102 Cut Sheet



ProSense signal conditioner, isolated, current transmitter input, current output, 6-35 VDC loop powered operating voltage, 35mm DIN rail mount, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SC6-4102>

Technical Specifications

Brand	ProSense
Item	Signal conditioner
Isolation	Isolated
Field Configurable	No
Input Current Signal Range	3.5-23 mA transmitter
Output Current Signal Range	3.5-23 mA
Operating Voltage	6-35 VDC loop powered
Housing Material	Plastic
Mounting	35mm DIN rail
Electrical Connection	Screw terminals

Agency Approvals

UL Listed File #	E498965
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	FM Approval Document