

# SC6-6102 Cut Sheet



ProSense temperature transmitter, non-isolated, RTD input, deg C or deg F, current output, 3.3-35 VDC loop powered operating voltage, 35mm DIN rail mount, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SC6-6102>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Temperature transmitter
<b>Isolation</b>	Non-isolated
<b>Field Configurable</b>	Yes
<b>Input RTD Signal Types</b>	Pt100
<b>Programmable Temperature Range</b>	Deg C or deg F
<b>Output Current Signal Range</b>	4-20 mA and 20-4 mA
<b>Operating Voltage</b>	3.3-35 VDC loop powered
<b>Housing Material</b>	Plastic
<b>Mounting</b>	35mm DIN rail
<b>Electrical Connection</b>	Screw terminals

## Agency Approvals

<b>UL Listed File #</b>	E498965
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">FM Approval Document</a>