

# SC6-6200 Cut Sheet



ProSense temperature transmitter, isolated, RTD input, deg C or deg F, current or voltage output, 24 VDC nominal operating voltage, 35mm DIN rail mount, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SC6-6200>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Temperature transmitter
<b>Isolation</b>	Isolated
<b>Field Configurable</b>	Yes
<b>Input RTD Signal Types</b>	Pt100
<b>Programmable Temperature Range</b>	Deg C or deg F
<b>Output Current Signal Range</b>	0-20 mA and 4-20 mA
<b>Output Voltage Signal Range</b>	0-5 VDC, 1-5 VDC, 0-10 VDC and 2-10 VDC
<b>Operating Voltage</b>	24 VDC nominal
<b>Housing Material</b>	Plastic
<b>Mounting</b>	35mm DIN rail
<b>Electrical Connection</b>	Screw terminals

## Agency Approvals

<b>UL Listed File #</b>	E498965
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">FM Approval Document</a>